

### Mounting

The TIP-ON unit can be either bored into the cabinet end panel or a attached to the cabinet interior using adapter plates.



## **Catch plate**

The catch plate is the counterpart to TIP-ON. It is available in self-adhesive or screw-on versions.



### **Hinges**

Free swing hinges are used with TIP-ON for doors with magnet/self close hinges are used with TIP-ON for doors with bumper.



Doors can be opened easily with TIP-ON - a light touch is all that's needed

- Designed for panel or face frame (blocked out) cabinet applications
- Works with CLIP top BLUMOTION, CLIP top, CLIP, COMPACT BLUMOTION and COMPACT
- Can be bored into the side panel or used with an adapter plate
- Easy depth adjustment for proper door gap setting
- Works for both overlay and inset applications
- Quick and easy installation
- Increased design options
- Requires minimal force to open and close

#### Tool-free door gap adjustment


The adjustment feature (+4/-1 mm) has been incorporated into the TIP-ON unit so even when TIP-ON is inserted into the cabinet, it has an integrated gap adjustment. To adjust gap, turn the ejector pin. The click-stop positions allow you to easily find the right setting.


**General specifications** 














±12" in height and up to a


terms of width.


quarter of the cabinet width in

# **TIP-ON for doors**









# **General specifications**



